
SGU4006EU/07-V08,graphit



Mat. - Nr. - Konstante 3740

Gebrauchsanweisung 52 0010 (D,GB,F,NL) Montage- / Aufstellanweisung 52 0359

Zubehör:

Entkalker 46 0038

Verlg. Aqua-Stop Kunststoffrohr 2,2 m


Ablaufschl. 1,95m SGZ1010

Messerkas.-Backbl.-Düse SGZ1000

Kupferrohr \emptyset 10 mm / 1,5 m SMZ3005


SGU4002/01-V02,weiß SGU4005EU/01-V03,edelstahl SGU4006EU/01-V04, graphit


SGU4000/07-V05,merian SGU4002/07-V06,weiß SGU4005EU/07-V07,edelstahl SGU4006EU/07-V08,graphit



BOSCH

SGU4000/07-V05,merian SGU4002/07-V06,weiß SGU4005EU/07-V07,edelstahl SGU4006EU/07-V08,graphit







BOSCH

SGU4000/01-V01,merian SGU4002/01-V02,weiß SGU4005EU/01-V03,edelstahl SGU4006EU/01-V04, graphit

SGU4005EU/07-V07,edelstahl SGU4006EU/07-V08,graphit



Mat. - Nr. - Konstante 3740 SGU4000/01-V01,merian SGU4002/01-V02,weiß SGU4005EU/01-V03,edelstahl SGU4006EU/01-V04,graphit SGU4000/07–V05,merian SGU4002/07–V06,weiß SGU4005EU/07–V07,edelstahl SGU4006EU/07–V08,graphit



Mat. – Nr. – Konstante 3740 merian SGU4000/07-V05,merian weiß SGU4002/07-V06,weiß 03,edelstahl SGU4005EU/07-V07,edelstahl 04,graphit SGU4006EU/07-V08,graphit



BOSCH